

Datasheet

RS Pro PVC Coated Galvanised Steel Flexible Conduit Black 25mm IP54 10m

RS Stock No: **668-4780**



Product Details

RS Pro cable conduit is 10 m long with a nominal diameter of 25 mm. It is made of galvanised steel with the addition of a thin, vacuum extruded PVC exterior coating, providing excellent weather protection without restricting the inner core flexibility. This IP40 rated conduit is perfect for high temperature continuous flexing applications requiring high mechanical protection. It is designed for commercial and industrial installations, including lighting, underfloor distribution, heating etc.

Features and Benefits

- IP54 rated
- Temperature range of -20 to +80°C
- Comes in black colour
- Self extinguishing to UL94 V0



Specifications:

| | |
|-------------------------------|------------------|
| Coating Material | PVC |
| Colour | Black |
| Conduit Type | Flexible |
| IP Rating | IP54 |
| Length | 10 m |
| Material | Galvanised Steel |
| Maximum Operating Temperature | +80°C |
| Minimum Operating Temperature | -20°C |
| Nominal Diameter | 25 mm |
| Operating Temperature Range | -20 to +80°C |
| | |