

# 03 06 180

## Combination Pliers



- with gripping zones for flat and round material, suitable for versatile use
- with cutting edges for soft and hard wire
- long cutting edges for thicker cables
- cutting edges additionally induction hardened, cutting edge hardness approx. 60 HRC
- Special tool steel, forged, oil-hardened



<b>Article No.</b>	03 06 180
<b>EAN</b>	4003773021926
<b>Pliers</b>	chrome plated
<b>Handles</b>	insulated with multi-component grips, VDE-tested
<b>Head</b>	
<b>Insulation standard</b>	IEC 60900 DIN EN 60900
<b>medium hard wire Ø mm</b>	3,4
<b>hard wire Ø mm</b>	2,2
<b>Cutting capacity copper cable, multiple-stranded (diameter) Ø mm</b>	12,0
<b>Cutting capacity copper cable, multiple-stranded mm<sup>2</sup></b>	16,0
<b>Nominal size</b>	180 mm
<b>Length mm</b>	180
<b>Net weight g</b>	264

technical change and errors excepted

