


Pressure screw - HC-DS-PG29-T - 1772719

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Pressure screws, with flared cable guard, clamping area 20 mm ... 27 mm, for housing with Pg29 support



Key commercial data

Packing unit	10 pc
GTIN	 4 017918 037369
Weight per Piece (excluding packing)	81.28 g
Custom tariff number	74153300
Country of origin	Germany

Technical data

Dimensions

Clamping range of the strain relief clip	20.00 mm ... 27.00 mm
--	-----------------------

General

Material, pressure screw	Nickel-plated brass
Thread type on connection side	Pg29

Classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

Pressure screw - HC-DS-PG29-T - 1772719

Classifications

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441

UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST

Drawings

Dimensioned drawing

