

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD


F

REV & REDRAW / 0720-0575-95

28SEP95

MLE

NB



- △ STAMP AMP 16-14 HD* APPROX AS SHOWN
2. WIRE INSUL DIA, 3.81-6.35 [.150-.250]
3. TONGUE MATERIAL THK, 1.22±0.05 [.048±.002]

---	-----	-----
50	LOOSE PIECE, BOX	8-35106-2
2500	ON TAPE, REEL	2-35106-1
500	LOOSE PIECE	35106
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMMAX RECOMMENDED OPERATING
TEMPERATURE:
105°C [221°F]THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DWN /3 T/3. T/

M ELLIS

CHK

C PRESNELL

APVD

N BIRCH

PRODUCT SPEC

UL 486A

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

AMP Incorporated
Harrisburg, PA 17105-3608NAME
TERMINAL, RING TONGUE, PIDG™,
WIRE SIZE, 16-14 HD AWGSIZE
A3CAGE CODE
00779DRAWING NO
C-35106SCALE
4:1SHEET
1 OF 1REV
FFOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER
1-800-522-6752FOR APPLICATION
TOOLING INFORMATIONTOOLING ASSISTANCE CENTER
1-800-722-1111


FOR ORDER ENTRY

1-800-526-5142

VOLTAGE RATING:
300 V MAXCIRCULAR MIL AREA:
1.04mm²-2.62mm² [2050-5180]

DIMENSIONS:

mm [in]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ±-
1 PLC ±-
2 PLC ±0.20 [.008]
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL

BODY, SLV, COPPER PER ASTM B 152

INSUL, NYLON, COLOR, YELLOW

FINISH

BODY & SLV, TIN PLATE

PER MIL-T-10727