



ENGLISH

Datasheet

Stock No: 235-887

RS Pro Xenon Beacon, Flashing, Surface Mount, 230 V ac



Product Details

Xenon Beacons, Single/Double Flash

Weatherproof and dustproof to IP56 these beacons offer high quality solutions for industrial environments and process applications.



ENGLISH

- Nominal flash output of 5J
- Optional single or double flash
- Approximately 80 flash per minute
- High protection rating of IP56
- Optional cage guard available
- Surge protection for safety against peak voltage
- Full internal suppression for maximum interference reduction
- Operating temperature range: -30°C to +50°C
- 166mm diameter
- Three point mounting

Note

Lens must be purchased separately

Supplied with

Bulb

Specifications:

Supply Voltage	230 V ac
Light Effect	Flashing
Lens Colour	Lens Not Included
Mounting Style	Surface Mount
Bulb Type	Xenon
Current Type	AC
Base Diameter	166mm
Housing Colour	Black
Lamp Included	Yes
Series	V10993
Height	207mm
Minimum Temperature	-30°C
Maximum Temperature	+50°C