

367 TORX® BO Screwdriver for tamper-proof TORX® screws










Application: TORX® screws with safety pin
(BO = with bore hole)

Blade: Round

Design: Bore hole in TORX® section, chrome-plated, Black Point

Handle: Kraftform with non-roll feature, multi-component

						
Code		mm	mm	mm		
05138257001	TX 7	60	70	3.5	2 3/8"	5
05138258001	TX 8	60	81	3.5	2 3/8"	5
05138259001	TX 9	60	81	4.0	2 3/8"	5
05138267001	TX 9	300	81	4.0	12"	5
05138260001	TX 10	80	81	4.0	3 1/8"	5
05138268001	TX 10	300	81	4.0	12"	5
05138261001	TX 15	80	98	4.0	3 1/8"	5
05138269001	TX 15	300	98	4.0	12"	2
05138262001	TX 20	100	98	4.5	4"	5
05138270001	TX 20	300	98	4.5	12"	2
05138263001	TX 25	100	105	5.0	4"	5
05138264001	TX 27	115	105	5.5	4 9/16"	5
05138265001	TX 30	115	105	6.0	4 9/16"	5
05138266001	TX 40	130	112	7.0	5 3/16"	5