

Conductor marker carrier - PATG 2/23 - 1013850

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marker carrier, transparent, unlabeled, Mounting type: slide on, Cable diameter: 2-4 mm, Lettering field: 4 x 23 mm

The figure shows version

Why buy this product

- ✓ The corresponding UC-WMT ..., US-WMT ..., and EMT insert labels are used for marking
- ✓ These conductor marking systems consist of marker carriers and insert labels
- ✓ The PATG ... collar is a captive marker carrier
- ✓ Can be used to mark conductors with a diameter of 0.6 ... 50 mm

Key Commercial Data

Packing unit	500 pc
Minimum order quantity	500 pc
GTIN	 4 017918 014049
Weight per Piece (excluding packing)	0.38 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Width (a)	23 mm
Cable diameter	2 mm ... 4 mm

Ambient conditions

Ambient temperature (operation)	-50 °C ... 80 °C
---------------------------------	------------------

General

Color	transparent
Components	Silicone-free
Flammability rating according to UL 94	V0
Material	PVC
RoHS compliant	Yes
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02

Conductor marker carrier - PATG 2/23 - 1013850

Technical data

General

Result	Test passed
Marking mounting type	slide on

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410