




FEMALE END VIEW



SPECIFICATIONS


HOUSING MATERIAL/COLOR	GLASS FILLED NYLON/BLACK
CONTACT MATERIAL/PLATING	GOLD PLATED BRASS
COUPLING NUT MATERIAL/PLATING	ANODIZED ALUMINUM
CAP MATERIAL/FINISH	NICKEL-PLATED BRASS
GASKET MATERIAL	NITRILE (BUNA-N)
O-RING MATERIAL	NITRILE (BUNA-N)
CABLE MATERIAL	STAINLESS STEEL/NYLON COATED
RATED CURRENT [A]	9.0 A
RATED VOLTAGE [V]	600 V
MAXIMUM WIRE SIZE	16 AWG
TERMINATION METHOD	SCREW TERMINAL
CABLE GRIP RANGE	PG 9 = 6-8mm, PG 13.5 = 10-12mm
TEMPERATURE RATING	-40°C to +90°C (-40°F to +194°F)
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP 67



SOURCE DRAWING - FOR REFERENCE ONLY

NOTES:

1. "/CS10359" DESIGNATES FIELD WIRABLE WITH CABLE CLOSURE CAP.

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		TURCK INC High Technology Sensors and Automation Controls 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com				
								
MATERIAL	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	DRFT	JB	DATE	02/27/02	DESCRIPTION B 4151-0/16/CS10359		
SEE SPECIFICATIONS		APVD		SCALE	1=1.0			
FINISH		UNIT OF MEASUREMENT				IDENTIFICATION NO.		REV
SEE SPECIFICATIONS		MILLIMETER [INCH]				U0878-09		B
		DO NOT SCALE THIS DRAWING				FILE: U0878-09		SHEET 1 OF 1

B	UPDATE CAP FROM THREE FLATS TO TWO	RDS	10/17/11	36728
REV	DESCRIPTION	BY	DATE	ECO NO.