

Screw connection - WP-GR HF IP69K PG16 BK - 3240933

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cable gland, Pg thread, IP68/69k protection, with strain relief

The figure shows the WP-GR HF IP69K M12 BK version



Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 046356 710404 |
| Weight per Piece (excluding packing) | 22.51 g |
| Custom tariff number | 39174000 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|------------------|----------|
| Height | 72 mm |
| Width (a) | 29.5 mm |
| Wrench size | 27.00 mm |
| Outside diameter | 21.20 mm |

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 115 °C |
| Degree of protection | IP68/IP69K |

General

| | |
|------------|--|
| Color | black |
| Type | With strain relief |
| | Outer thread |
| Components | free from silicone, halogen, and cadmium |

Screw connection - WP-GR HF IP69K PG16 BK - 3240933

Technical data

General

| | |
|---|----|
| Inflammability class according to UL 94 | V0 |
| Material | PA |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27141131 |
| eCl@ss 4.1 | 27141131 |
| eCl@ss 5.0 | 27141131 |
| eCl@ss 5.1 | 27141120 |
| eCl@ss 6.0 | 27141120 |
| eCl@ss 7.0 | 27141120 |
| eCl@ss 8.0 | 27149109 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC000897 |
| ETIM 4.0 | EC001178 |
| ETIM 5.0 | EC000441 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211812 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121411 |
| UNSPSC 12.01 | 39121411 |
| UNSPSC 13.2 | 39121411 |

Approvals

Approvals

Approvals

UL Recognized / VDE Zeichengenehmigung / LR


Ex Approvals


Approvals submitted

Approval details

Screw connection - WP-GR HF IP69K PG16 BK - 3240933

Approvals

UL Recognized 

VDE Zeichengenehmigung 

LR

Accessories

Accessories

Corrugated pipe

Protective hose - WP-PA HF 21,2 BK - 3240683



Polyamide protective hose, inflammability class V0, UV resistant, 1 Pcs. / Pkt. = roll à 50 m

Protective hose - WP-PA HF-HB 21,2 BK - 3240841



Polyamide protective hose, inflammability class HB, UV resistant, 1 Pcs. / Pkt. = roll à 50 m

Mounting material

Protective hose fixing bracket - WP-BASE A PG16 - 3241079



Fixing bracket for protective sleeves, fixed with two screws