

Flange - PT 2,5-4L/1P-FS - 3012302

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Flange, Length: 105.6 mm, Width: 5.2 mm, Color: gray



Why buy this product

- The Push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors
- The compact design and front connection enable wiring in a confined space
- In addition to the testing facility in the double function shaft, all terminal blocks provide an additional test connection



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 672405
Weight per Piece (excluding packing)	12.33 g
Custom tariff number	85472000
Country of origin	Poland

Technical data

General

Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

Dimensions

Width	5.2 mm
End cover width	2.2 mm
Length	105.6 mm
Height NS 35/7,5	59 mm
Height NS 35/15	66.5 mm

Flange - PT 2,5-4L/1P-FS - 3012302

Classifications

eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27141145
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120

ETIM

ETIM 3.0	EC001922
ETIM 4.0	EC001922
ETIM 5.0	EC002498

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121411
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Accessories

Accessories

Cover profile

Flange - PT 2,5-4L/1P-FS - 3012302

Accessories

Cover profile - AP-CP-H CM - 3000801



Cover profile for covering terminal strips, snaps onto cover profile carrier APT-ME or end clamp APH-ME. A cover profile carrier is to be positioned at the ends and at intervals of around 40 cm. Length as per customer requirement.

Cover profile - AP-CP-H METER - 3012315



Cover profile, length: 1 m

Documentation

Mounting material - PT-IL - 3208090

Operating decal for the push-in Technology



Jumper

Plug-in bridge - FBSR 2-5 - 3033702



Plug-in bridge, Number of positions: 2, Color: red

Plug-in bridge - FBSR 3-5 - 3001591



Plug-in bridge, Number of positions: 3, Color: red

Flange - PT 2,5-4L/1P-FS - 3012302

Accessories

Plug-in bridge - FBSR 4-5 - 3001592



Plug-in bridge, Number of positions: 4, Color: red

Plug-in bridge - FBSR 5-5 - 3001593



Plug-in bridge, Number of positions: 5, Color: red

Plug-in bridge - FBSR 10-5 - 3033710



Plug-in bridge, Number of positions: 10, Color: red

Planning and marking software

Software - CLIP-PROJECT ADVANCED - 5146040



Multilingual software for easy planning of Phoenix Contact on DIN rails together with the integrated TRABTECH-select software module for planning comprehensive surge protection concepts.

Software - CLIP-PROJECT PROFESSIONAL - 5146053



Multi-lingual software for terminal strip project planning. A marking module allows professional labeling of markers and labels for marking terminal blocks, conductors, cables and devices. The additionally integrated software module TRABTECH-select for planning comprehensive surge protection concepts.

Plug

Flange - PT 2,5-4L/1P-FS - 3012302

Accessories

Connector housing - CP-H 2,5-4L - 3012313



Connector housing, Length: 31.6 mm, Width: 5.2 mm, Height: 31.7 mm, Number of positions: 1, Color: gray

Connector housing - CP-H 2,5-4L-Z - 3012314



Connector housing, Length: 31.6 mm, Width: 5.2 mm, Height: 31.7 mm, Number of positions: 1, Color: gray

Connector housing - CP-H 2,5-4L BU - 3012322



Connector housing, Length: 31.6 mm, Width: 5.2 mm, Height: 31.7 mm, Number of positions: 1, Color: blue

Terminal plug

Connector housing - CP 2,5-4L-Z - 3041943



Connector housing, Connection method: Special and hybrid connection, Number of positions: 1, Cross section: 0.5 mm² - 2.5 mm², AWG: 20 - 14, Width: 5.2 mm, Height: 13 mm, Color: gray

Connector housing - CP 2,5-4L - 3041956



Connector housing, Connection method: Special and hybrid connection, Number of positions: 4, Cross section: 0.5 mm² - 2.5 mm², AWG: 20 - 14, Width: 5.2 mm, Height: 13 mm, Color: gray

Additional products

Flange - PT 2,5-4L/1P-FS - 3012302

Accessories

Flange cover - DFS-CP-H 2,5-4L - 3012317



Self-locking flange cover as a cover profile carrier, for CP-H 2,5-4L, can be adapted on both sides of the plug

Flange cover - DFS-CP 2,5-4L - 3012321



Flange cover, Length: 31.6 mm, Width: 5.2 mm, Height: 26 mm, Color: gray
