

### General Information

Extended Product Type:	JSHT1B 24DC
Product ID:	2TLA010011R1000
EAN:	7350024432831
Catalog Description:	JSHT1B 24DC Time module
Long Description:	Safety timer for time reset and time bypassing. Hardwired time selection 5-40 sec. Relay outputs 1NO+1NO

### Categories

Products » Low Voltage Products and Systems » Control Products » Electronic Relays and Controls » Safety Relays  
 Products » Low Voltage Products and Systems » Control Products » Safety Products » Safety Relays

### Ordering

EAN:	7350024432831
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85364110

### Dimensions

Product Net Width:	0.045 m
Product Net Height:	0.074 m
Product Net Depth:	0.120 m
Product Net Weight:	0.330 kg

### Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	0.131 m
Package Level 1 Height:	0.057 m
Package Level 1 Length:	0.081 m
Package Level 1 Gross Weight:	0.365 kg

### Safety Information

Safety Category Acc. to ISO 13849-1: 4

### Additional Information

Product Main Type:	JSH
Product Name:	Safety Timer
Rated Control Supply Voltage (U <sub>s</sub> ):	24 V DC
Suitable For:	Time resetting, Time bypassing

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	2TLC172001C0202_chapter06
Declaration of Conformity - CE:	2TLC172078D0201

### Classifications

ETIM 4.0:	EC001449 - Device for monitoring of safety-related circuits
ETIM 5.0:	EC001449 - Device for monitoring of safety-related circuits
Object Classification Code:	K

