



Sample photo

Order symbol: AL 061005
Product nbr: 7011080
Description: Enclosure
Remarks: Aluminium

EAN: 6418074004093
EI. number:
 Finland 3423605
 Denmark 8212004621
 Italy 7321020
 Sweden 2536307

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:	L	W	H
mm:	66	100	46
inch:	2.6	3.9	1.8

Rating:
Ingress Protection (EN 60529): IP 66/67
Impact Resistance (EN 50102): IK 08
NEMA Class: NEMA 1, 4, 4X, 12, 13

Materials:
Material: AL
Base colour: RAL 7001
Cover colour: RAL 7001
Cover screws material: Stainless steel
Gasket material: Polyurethane

Certificates:
Underwriters Laboratories
UL Canada

Temperatures:
Short term: -50 ... 140 °C
Continuous: -50 ... 80 °C
Short term: -60 ... 285 °F
Continuous: -60 ... 175 °F

Accessories:	
ARM 0610	DIN-15 Mounting rail
MR 75003	Taptite screw
MRS 28540	Wall fastening lug set

