

Datasheet

**RS Pro Zinc Plated Steel Adjustable Height Mount 98mm
Rubber 115mm 45mm 158mm 1000kg 120mm M12 3.5°
RS Stock No: 283-1783**



Product Details

RS Pro adjustable height mount is a zinc plated steel machine mount, which is suitable for use in less demanding environments. It is designed for use in applications that impose strict safety and reliability demands on the installation and damping of light and medium duty machinery. It has a thread size of M12 and diameter of 98 mm. The foot material of mount is made from rubber and has an adjustable height from 45 to 115 mm. It has a static load capacity of 1000 kg and a thread length of 120 mm with a tilt angle of 3.5°.

Features and Benefits

- Long bolt offers height adjustment
- Compensates with up to 7° swivel
- For use in applications that impose strict safety and reliability demands on the installation and damping of light and medium duty machinery
- Built in levelling bolt means the stainless steel mounts can be adjusted within a large range with considerable accuracy, allowing a 7° inclination while still maintaining stability



Specifications:

Base Material	Zinc Plated Steel
Diameter	98 mm
Foot Material	Rubber
Maximum Adjustment Height	115 mm
Minimum Adjustment Height	45 mm
Overall Height	158 mm
Static Load Capacity	1000 kg
Thread Length	120 mm
Thread Size	M12
Tilt Angle	3.5°