

Specifications for TLS 2200/TLS PC Link Fibre Optic Labels/Flags

Adhesive	Permanent Acrylic
Application	Voice & Data Communication
Approval/Compliance	UL Recognised; CSA Accepted; Halogen Free (DIN VDE 0472/part 815)
Article No.	217021
Brady Material No.	B-425
Material Type	Polypropylene
Brand	WorkHorse™ Series
Colour	White
Finish	Matt
Description	Flags for the TLS2200® & TLS PC Link™ Thermal Transfer Portable Printers. TLS2200® parts can also be printed on the BMP™71 Label Printer provided the roll adapter (M71-ADAPT) is used.
Max. Characters per Line	26
Max. Lines of Text	3
Max. Service Temp. °C	80
Order Reference	PTLFT-01-425
Printable Area - Height (mm)	10.00
Printer Compatibility	BMP71; TLS2200; TLSPC Link
Ribbon Series	R4310
Shape	Rectangle
Size - Height (mm)	20.00
Size - Width (mm)	30.00
Additional Information	Excellent solvent resistance
Total Qty per Pack	250 Label(s) / Roll
Voice/Data	Fibre Optic Labels/Flags: Pig-tail and single fibre Identification

