

## WR 2 - Repair Station

BestellNr.:0053377699



### WR 2 Power Unit 300 W

The new WR 2 has been designed to deliver high performance at an affordable price. Want a station that will allow you to work on both soldering and desoldering operations at the same time or soldering and hot air tasks - then the WR 2 is for you. This new repair station from Weller is based on our highly successful WR 3M product range and with its 2 channel design it represents a great price/performance package. In use this new station more than lives up to Weller's high quality reputation and has the added advantage of being connectable to all of Weller's High Power Tools range of products. These tools allow operators to work more efficiently both in terms of time and energy as well as helping to extend tip life time. The 2 channels of the WR 2 power unit allow a soldering and desoldering tool or a soldering and hot air tool to be connected and operated simultaneously. In addition, to save on power consumption, an ECO function on the unit allows the tools to go into a "sleep mode" when not in use.

### Top Attributes

- 2 independent tool channels with automatic tool recognition
- Simultaneous use of 2 tools (up to maximum 300 W power rating of the unit)
- Weller MicroTools are not connectable
- Will drive all Weller 200 W soldering and desoldering irons
- Self contained vacuum and air turbine
- ECO button for "sleep mode"
- Programmable temperature memory key
- ESD safe

### Technical Data

|   |              |
|---|--------------|
| Display technology                                | LC           |
| Equipotential Bonding/ hard grounding explanation | Normal state |
| Temperatur control comment                        | Button       |
| Display included & Size                           | Large        |
| Certifications                                    | .            |

|                                       |             |
|---------------------------------------|-------------|
| Display information content           | High        |
| ESD safe                              | Yes         |
| Equipotential Bonding/ hard grounding | Yes         |
| Display backlight                     | No          |
| Antistatic housing                    | Yes         |
| Max. vacuum                           | 0.7 bar     |
| Air volume hot air                    | 10.0 l/min  |
| Temperature stability                 | 5 °C        |
| Power unit wattage                    | 300 W       |
| Mains supply Voltage                  | 230 V       |
| Power supply frequency                | 50 Hz       |
| Output voltage                        | 230 V       |
| Protection class Soldering iron       | 3           |
| Protection class Control/ Power unit  | 1           |
| Temperature accuracy                  | 9 °C        |
| Temperature regulation                | 50 - 550 °C |

## Packaging information

|  |   |
|--|---|
| Shelf pack size (Units per shelf pack) | 1 |
|--|---|