




REV	DESCRIPTION	DATE
-----	-------------	------

NOTE:

1. MAXIMUM ELECTRIC CURRENT: 10 AMPERE
2. MAXIMUM ELECTRICAL RATING: 125°C 300 VOLTS MAX.
3. INSULATION MATERIAL: PC
4. INSULATION COLOR: RED
5. TERMINAL MATERIAL: BRASS
6. WIRE RANGE: 22-16A.W.G. (0.5-1.5mm²)
7. TERMINAL THICKNESS: 0.40mm
8. NEMA TAB: .032*.250 (0.8*6.35)

Tolerance Unless Otherwise Specified			
0 >	mm ±	ANGLE	
>	mm ±	0°	REF ±
>	mm ±	°	±
>	mm ±	°	±

NAME	PC-INSULATED FEMALE DISCONNECTORS				UNIT	mm	
PART NO.	FDNI1-250	MATERIAL			APPROVE		
NUMBER	TNV-472	SCALE	SHEET	PAGE	CHECKED		
DATE	11/24/2004	3 : 1	1-0	1 OF 1	DRAWN		

KST K.S. TERMINALS INC.