

# Housing - HC-B 10-TFQ-N-O1STM25S - 1460067

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON B10 sleeve housing, for double locking latch, height: 56 mm, with 1 x M25 thread, lateral cable outlet



## Key commercial data

|                                      |  |
|--------------------------------------|--|
| Packing unit                         | 10 pc  |
| GTIN                                 | <br>4 046356 695688 |
| Weight per Piece (excluding packing) | 22.22 g  |
| Custom tariff number                 | 85389099   |
| Country of origin                    | Germany  |

## Technical data

### Dimensions

|        |       |
|--------|-------|
| Height | 56 mm |
| Width  | 43 mm |
| Length | 73 mm |

### Ambient conditions

|                                      |                   |
|--------------------------------------|-------------------|
| Degree of protection of housing (IP) | IP65              |
| Ambient temperature (operation)      | -40 °C ... 125 °C |

### General

|                              |  |
|------------------------------|--|
| Note                         | For contact inserts HC-B10, BB18, DD42, M, K8/24 |
| Type                         | B10  |
| Housing type                 | Sleeve housing                                   |
| Locking type                 | For double locking latch                         |
| No. of cable outlets         | 1  |
| Cable exit                   | Lateral  |
| Screw connection             | none   |
| Type of the screw connection | 1x M25   |
| Housing material             | Aluminum die-cast                                |

# Housing - HC-B 10-TFQ-N-O1STM25S - 1460067

## Technical data

### General

|                          |                     |
|--------------------------|---------------------|
| Housing surface material | Powder-coated, gray |
|--------------------------|---------------------|

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27140816 |
| eCl@ss 4.1 | 27140816 |
| eCl@ss 5.0 | 27143424 |
| eCl@ss 5.1 | 27143424 |
| eCl@ss 6.0 | 27143424 |
| eCl@ss 7.0 | 27440209 |
| eCl@ss 8.0 | 27440202 |

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000437 |
| ETIM 4.0 | EC000437 |
| ETIM 5.0 | EC000437 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 31261502 |
| UNSPSC 7.0901 | 31261502 |
| UNSPSC 11     | 31261502 |
| UNSPSC 12.01  | 31261502 |
| UNSPSC 13.2   | 31261502 |

## Approvals

### Approvals

---

#### Approvals

EAC

---

#### Ex Approvals

---

#### Approvals submitted

---

### Approval details

|     |
|-----|
| EAC |
|-----|

## Housing - HC-B 10-TFQ-N-O1STM25S - 1460067

### Accessories

#### Accessories

#### Extension adapter

Extension adapter - ENLAR-M-KV-M25/M32 - 1647679



Step-up adapter, M25 to M32, including O-ring

---

#### Full screw connection

Cable gland - G-INS-M25-M68N-PNES-GY - 1411126



Cable gland, Cable gland material: Polyamide 6, External cable diameter 11 mm ... 17 mm, Shielding: No, Connecting thread: M25, Color: silver grey

---

Cable gland - G-INS-M25-M68N-PNES-BK - 1411134



Cable gland, Cable gland material: Polyamide 6, External cable diameter 11 mm ... 17 mm, Shielding: No, Connecting thread: M25, Color: jet black

---

Cable gland - G-INS-M25-M68N-NNES-S - 1411165



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 11 mm ... 17 mm, Shielding: No, Connecting thread: M25, Color: silver

---

Cable gland - HC-M-KV-M25(14-21) - 1646007



Metal screw connection up to 5 bar, thread length: 7 mm, cable diameter: 14 - 21 mm, WAF 34, screw connection: M25

---

## Housing - HC-B 10-TFQ-N-O1STM25S - 1460067

### Accessories

Cable gland - G-INSEC-M25-S68N-NCRS-S - 1411190



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 11 mm ... 16 mm, Shielding: Yes, Connecting thread: M25, Color: silver

Cable gland - HC-M-KV-Z-M25 - 1646159



Metal screw connection with strain relief clamp, thread length: 7 mm, cable sealing area: 10 - 19 mm, clamping area: 12 - 22 mm, SW 30, screw connection: M25

Cable gland - HC-M-KV-T-M25 - 1646191



Metal screw connection with cable bend protection and strain relief, thread length: 7 mm, cable sealing area: 10 - 19 mm, clamping area: 14 - 21 mm, SW 30, screw connection: M25

Plug for cable screw gland

Filler plugs - HC-M-BS-M25 - 1645859



Filler plug, metal, size: M25

Reducing adapter

Reducing adapter - REDUC-M-KV-M25/M20 - 1647624




Step-down adapter, M25 to M20, including O-ring

Drawings

## Housing - HC-B 10-TFQ-N-O1STM25S - 1460067

Dimensioned drawing



Dimensional drawing

---