



Sample photo

Order symbol: ALN 081806
Product nbr: 7811170
Description: Enclosure
Remarks: Aluminium

EAN: 6418074016089
El. number:
Finland:
:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

| Dimensions: | | Length | Width | Height | Rating: |
|-------------------------------|------------------------------|--------|-------|--------|---|
| mm: | | 177 | 81 | 57 | Ingress Protection (EN 60529): IP 66/67/68 |
| inch: | | 7.0 | 3.2 | 2.2 | Impact Resistance (EN 62262): IK 08 |
| Materials: | | | | | NEMA Class: NEMA 1, 4, 4X, 12, 13 |
| Material: | Aluminium | | | | Certificates: Underwriters Laboratories Fimko UL Canada Gost R |
| Base colour: | RAL 7001 | | | | |
| Cover colour: | RAL 7001 | | | | |
| Cover screws material: | Stainless steel | | | | |
| Gasket material: | Polyurethane | | | | |
| Temperatures: | | | | | |
| Short term: | -50 ... 140 °C | | | | |
| Continuous: | -50 ... 80 °C | | | | |
| Short term: | -60 ... 285 °F | | | | |
| Continuous: | -60 ... 175 °F | | | | |
| Accessories: | | | | | |
| AM 0818 | Mounting plate | | | | |
| ARM 0818 | DIN-15 Mounting rail | | | | |
| EKV 12 | DIN-35 Mounting rail | | | | |
| MR 75003 | Selftapping taptite screw M3 | | | | |
| MRS 28540 | Wall fastening lug (2 pcs) | | | | |

