






MATING CONNECTOR INTERFACE



2.67	.105	7.62	.300	—	—
2.13	.084	5.08	.200	—	—
1.57	.062	5.05	.199	19.05	.750
0.64	.025	3.68	.145	18.62	.733
0.25	.010	3.18	.125	16.21	.638
0.13	.005	2.79	.110	16.13	.635
MM	IN	MM	IN	MM	IN
CONVERSION TABLE					



		PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.13 3 PLC DEC ± - ANGLES ± 1°0'		DR 11-4-93 K. WHITAKER CHK 11-4-93 R. SWING APPD 11-4-93 C. CASH APPD 11-4-93 C. CASH PRODUCT SPEC -	
MATERIAL NYPN,UL 94V-2 NATURAL		NAME PLUG, 4 CIRCUIT, .062 PIN AND SOCKET	
FINISH -		SIZE D	CAGE CODE 00779
APPLICATION SPEC WEIGHT -		DRAWING NO C-770275	
		SCALE 5:1	SHEET 1 OF 1