


KEMET Part Number: PEH200KD5220MB2
(A451GK223M040A)

PEH200, Aluminum Electrolytic, 22,000 uF, 20%, 40 VDC, -40/+85°C



General Information

Supplier:	KEMET
Series:	PEH200
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
Mounting:	Stud
AEC-Q200:	No
Notes:	Dimensions D And L Include Slewing. MS = M8x12
Shelf Life:	156 Weeks

Dimensions

D	36.6mm +/-1mm
L	94.5mm +/-1mm
T	4.4mm NOM
S	13mm +/-0.5mm
DT	8mm NOM
LT	101.9mm +/-1mm

Packaging Specifications

Weight:	130 g
Slewing:	Yes
Packaging:	Bulk, Bag
Packaging Quantity:	42

Specifications

Capacitance:	22,000 uF
Capacitance Tolerance:	20%
Voltage DC:	40 VDC
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	10000 Hrs (Rated Voltage And Ripple Current At 85C)
Resistance:	12 mOhms (100Hz 20C), 9 mOhms (100kHz 20C)
Ripple Current:	17.1 Amps (100Hz 85C), 39.8 Amps (10kHz 50C), 29.2 Amps (10kHz 40C)
Leakage Current:	6640 uA (5min 20°C)
Inductance:	12 nH (ESL)