

Datasheet

RS Pro M12 Black Nylon Cable Gland With Lock Nut, 3 to 6.5mm Cable Dia Range, IP68

RS Stock No: **669-4658**



Product Details

RS Pro cable gland in black colour, has a thread size of M12. It has a cable diameter ranging from 3 to 6.5 mm. The cable made of plastic is IP68 rated. This nylon cable gland is supplied completely with lock nut and entry thread seal.

Features and Benefits

- Manufactured from UL approved nylon 66
- Flammability rating to UL 94V-2
- Provides watertight seal to IP68
- Offers strain relief and protection for cables

**Specifications:**

Cable Diameter Range	3 to 6.5 mm
Colour	Black
IP Rating	IP68
Locknut Included	Yes
Material	Nylon 66
Maximum Cable Diameter	6.5 mm
Maximum Operating Temperature	+85°C
Minimum Cable Diameter	3 mm
Minimum Operating Temperature	-60°C
Operating Temperature Range	-60 to +150°C
Standards Met	UL 94V-2
Thread Size	M12