

Material number	0 600 910 670
EAN	3165140810180
Adjustable 3-in-1 lance (stainless steel)	✓
Bosch gun	✓
Voltage 240 V	✓
Packaging dimensions (width x length x height)	440 x 785 x 398 mm
Voltage, electrical	240 V



Technical data

Technical data

Max. pressure	160 bar
Rated input power	2.400 W
Operating pressure	130 bar
Max. inlet temperature	50 °C
Cable length	5 m
Hose length	10 m
Material (hose)	Reinforced rubber hose
Weight (without accessories)	24 kg
Rated flow rate	485 l/h
Max. flow rate	520 l/h
Pump system	Wobble plate
Pistons	Steel
Motor type	Induction
Lance	Adjustable 3-in-1 lance (stainless steel)

Noise/vibration information

Sound pressure level	78 dB(A)
Sound power level	92 dB(A)
Uncertainty K	2.5 dB

Sales information

Positioning

- Powerful and versatile: A compact, mobile and powerful high-pressure washer with practical hose reel

User benefit

- High cleaning power: Aluminium anodised pump with stainless steel pistons producing a combination of high flow and pressure resulting in high cleaning power
- Convenient: Metal telescopic handle for ease of use. Mobile and space-saving due to hose reel
- Versatile: Used both in horizontal and vertical positions

