



ENGLISH

## RS Pro PUR 10m Long transparent Flexible Ducting Reinforced, 38mm Bend Radius , Applications Various

RS Stock No. 362-2164

Brand RS Pro



Image representative of range

# Product Details

## PU-R Medium Weight Polyurethane Ducting

An RS Pro Brand of polyurethane (PU) hosing with a copper-plated steel spiral. Designed for suction and the transport of dusts, chips and abrasive materials.

Copper coated spring steel spiral helix between two layers of crystal clear flexible polyurethane

Excellent internal and external abrasion resistance

Retains full diameter even in tight bending radii

Suitable for the transfer of large abrasive particles such as sawdust, timber offcuts and metal swarf

Also suitable for oil and petrol fume extraction

Temperature range -40 to +90°C

### Note

All data refers to performance at 18°C. Any change in temperature either above or below 18°C will affect the performance data.



## Specifications

Not what you're looking for? Select the attributes you require, then click the button below

<input type="checkbox"/>	Inner Diameter	38mm
<input type="checkbox"/>	Outer Diameter	43mm
<input type="checkbox"/>	Material	PUR
<input type="checkbox"/>	Length	10m
<input type="checkbox"/>	Suitable Applications	Abrasive Material, Chemical, Dust, Granule, Saw Dust
<input type="checkbox"/>	Colour	Transparent
<input type="checkbox"/>	Bend Radius	38mm
<input type="checkbox"/>	Reinforced	Yes