

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130111-0027](#)
Status: **Active**
Overview: [Stringlights](#)
Description: Safety Yellow® Molded Stringlight, 200W, 14/2 SJTW with 2.43m Lead 10 Sockets Guards Lamp-it-in-the-Box, Overall Length 30.48m (100.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

Agency Certification

UL E112216

General

Product Family Portable Lighting
 Series [130111](#)
 NEMA Configuration NEMA 1-15
 NEMA Rating Rain Tight
 Outlet None
 Overview [Stringlights](#)
 Product Literature Order No 987650-8055
 Product Name Safety Yellow®
 Type String Lights
 UPC 78678840867
 Woodhead Yes

Physical

Cord Length - Primary 2.43m (8.0')
 Cord Length - Secondary 0.61m (2.0')
 Depth N/A
 Duty Commercial
 Guard Included STR101
 Guard Type N/A
 Height N/A
 Length 30.48m (100.0')
 Material - Guard Polypropylene
 Mounting Style Stringer
 Packaging Type Carton
 Socket Construction Molded

Electrical

Bulb Type Incandescent
 Cord Type - Primary 14/2 SJTW
 Lamp Type A21
 Lamp Wattage - Maximum 200W
 Lumens 2000
 On/Off Switch No
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Old Part Number 5000



EU RoHS

**ELV and RoHS
 Compliant
 REACH SVHC
 Not Reviewed
 Low-Halogen Status
 Not Reviewed**

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130111Series