

TURCK

Level Sensors - Capacitive



Housing Style	Part Number	ID Number	Features	Embeddable Range (mm)	Nonembed. Range (mm)	Output
	BC20-Q20-AN4X2	M2530110		20	30	3-Wire DC NPN
	BC20-Q20-AN4X2/S400	M2530104	Rear LED	20	30	
	BC20-Q20-AP4X2	M2530100		20	30	3-Wire DC PNP
	BC20-Q20-AP4X2/S400	M2530102	Rear LED	20	30	
	BC20-Q20-VP4X2/S400	M2530122	Comp. Outputs Rear LED	20	30	4-Wire DC PNP
	BC20-Q20-AZ3X2	M4352000		20	30	2-Wire AC
	BC20-Q20-AZ3X2/S400	M2310005	Rear LED	20	30	

"/S400" in part number designates rear LEDs, located on back of sensor opposite of sensing face.

Level Sensors - Capacitive

Voltage	Switching Freq. (Hz)	Operating Current (mA)	Operating Temp. (°C)	Protection Class	Housing Material	Power LED	Output LED	CableLength /Jacket	Wiring Diagram #	Wiring Diagrams
10-65 VDC	100	≤200	-25 to +70	IP67	PBT-GF30-V0	GN	YE	2M/PVC	1	Diagram 1
	100	≤200	-25 to +70	IP67	PBT-GF30-V0	GN	YE	2M/PVC	1	
10-65 VDC	100	≤200	-25 to +70	IP67	PBT-GF30-V0	GN	YE	2M/PVC	2	Diagram 2
	100	≤200	-25 to +70	IP67	PBT-GF30-V0	GN	YE	2M/PVC	2	
10-65 VDC	100	≤200	-25 to +70	IP67	PBT-GF30-V0	GN	YE	2M/PVC	3	Diagram 3
20-250 VAC	20	≤500	-25 to +70	IP67	PBT-GF30-V0	GN	YE	2M/PVC	4	Diagram 4
	20	≤500	-25 to +70	IP67	PBT-GF30-V0	GN	YE	2M/PVC	4	