

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130105-0050](#)
Status: **Active**
Overview: Specialty Lighting
Description: LOVOLT® 400W 120V/12V Workstation with 4 Receptacles 15A Breaker, 16/3 SOOW Cord Type, 1.83m (6.0') Cord Length

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

General

Product Family	Portable Lighting
Series	130105
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 3R
Outlet	2 - 60W07 Non-NEMA Crow Foot
Overview	Specialty Lighting
Product Literature Order No	987650-8052
Product Name	Woodhead®
Type	Specialty Light
UPC	78678862520
Woodhead	Yes

Physical

Cord Length - Primary	1.83m (6.0')
Cord Length - Secondary	N/A
Depth	80.01mm (3.150")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	206.25mm (8.120")
Length	285.75mm (11.250")
Material - Guard	N/A
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	N/A
Cord Type - Primary	16/3 SOOW
Lamp Type	N/A
Lamp Wattage - Maximum	400W
Lumens	N/A
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Voltage (Secondary) - Maximum	12V AC

Material Info

Old Part Number	1640-12
-----------------	---------



EU RoHS

RoHS Compliant by Exemption

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130105Series](#)