




Einbauhöhe
mounting height




Bolzen / bolt :




Anschlussbereich verzinnt
terminal area tin plating

Anforderungsstufe: 2
class: 2

	177445	ø3,2			
	154258			#4-40	
	154257			M 3	
	154256		#4-40		
	154255		M 3		
Ident-Nr part-no. tape & reel	Ident-Nr part-no. tray	ohne without	Mutter thread	Bolzen bolt	Bemerkung remark




Verpackt in Tray
Verpackungseinheit 24 St.
tray packaging
packaging unit 24 pcs



Verpackt in Gurt
Verpackungseinheit 75 St.
tape & reel packaging
packaging unit 75 pcs

Abspulrichtung
reel off direction

Layout



Fehlende Masse und Angaben siehe DIN 41652 /

Missing information and dimensions according to DIN 41652

Sonstige Angaben siehe Fertigungsunterlagen /

Additional indications please see the production documentation

Information:	Tolerances ISO 2768-m		Scale 2:1	
All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.	Subject to modification without prior notice. Drawing will not be updated.	Designation TMC-S 15-THR-Standard TMC-S 15-THR-Standard	144856	
Index	Date	ERNI www.ERNI.com	V:00036635.SZN	TMC S

Consider protection memo from DIN 34