

ToLEDo Retro A60

ToLEDo RT CS A60 450LM E27 SL

0027157

Range features



PRODUCT OVERVIEW

| | |
|----------------------------|------------------|
| Ordering number | 0027157 |
| Technology | LED |
| Light colour | Homelight |
| Energy class | A++ |
| Average life (Rated) (h) | 15000 |
| Lamp shape | A60 |
| Lamp finish | Silvered Crown |
| Dimmable | No |
| Cap/Base | E27 |
| Type | ToLEDo Retro A60 |
| EAN code | 5410288271576 |
| CRI (Ra) | 80 |
| Colour temperature (K) | 2700 |
| Luminous flux (Rated) (lm) | 450 |
| Efficacy (Rated) (lm/w) | 112.5 |
| Watt (Nominal) (W) | 4 |
| Equivalent watt (W) | 39 |
| Voltage (V) | 220-240 |

ToLEDo Retro A60

ToLEDo RT CS A60 450LM E27 SL

0027157

DATA TABLE

General data

| | |
|--|-------------------------------------|
| Dry applications use only | Yes |
| Technology | LED |
| Ordering number | 0027157 |
| Energy saving lamp | Yes |
| Energy class | A++ |
| Average life (Rated) (h) | 15000 |
| Average life (Nominal) (h) | 15000 |
| Lamp finish | Silvered Crown |
| Lamp shape | A60 |
| Dimmable | No |
| Cap/Base | E27 |
| Type | ToLEDo Retro A60 |
| EAN code | 5410288271576 |
| Product name | ToLEDo RT CS A60 450LM E27 SL |
| Lamp mercury content (mg) | 0 |
| Starting time (max) (s) | 0.05 |
| Warm-up time to 60% of full light (max) (s) | < 1s => 60% |
| Control gear required | No |
| Control gear availability | No |
| General application | Hospitality; Residential & Consumer |
| Intended purpose | No |
| No. of switching cycles before premature failure (min) | >20000 |
| Special purpose lamp | No |
| Transformer required | No |
| Optimal operating condition (°C) | 25 |

Optical data

| | |
|--|-----------|
| Light colour | Homelight |
| CRI (Ra) | 80 |
| Suitable for accent lighting | No |
| Colour temperature (K) | 2700 |
| Luminous flux (Rated) (lm) | 450 |
| Lumen maintenance at end of nominal life (%) | 80 |
| Luminous flux (Nominal) (lm) | 450 |
| Adjustable chromaticity | No |

ToLEDo Retro A60

ToLEDo RT CS A60 450LM E27 SL

0027157

Electrical data

| | |
|---------------------------------|---------|
| kWh per 1000 hours burning time | 4 |
| Efficacy (Rated) (lm/w) | 112.5 |
| Watt (Nominal) (W) | 4 |
| Watt (Rated) (W) | 4 |
| Equivalent watt (W) | 39 |
| Voltage (V) | 220-240 |
| Drive current (mA) | 35 |
| Lamp power factor | 0.5 |

Physical data

| | |
|--|-----|
| Lamp Length (mm) - C/L | 105 |
| Max. Lamp Diameter (mm) - D | 60 |
| Lamp dimension equal to filament lamp equivalent | Yes |

ENERGY LABEL

