



ENGLISH

Datasheet

RS Pro VF White Flexible slot Cable Trunking Slotted Flexible Panel Trunking, W9 mm x D11mm, L500mm

RS Stock No: **598-591**



Product Details

RS Pro flexible slot cable trunking panel in white colour, measures 500 mm long with 9 mm wide and 11 mm deep. This polypropylene flexible slotted trunking panel with strong self adhesive backing, assist installation. The trunking panel has a round shape that possesses low flammability, halogen free and self extinguishing in accordance with UL94-V1 standard. The base has additional slots to accept further fixing if required (F.C. 50 mm) with a temperature range of -20 to +70°C.

**Specifications:**

Colour	White
Depth	11 mm
Fire Behaviour	Flame Retardant, Low Smoke Density, Self-Extinguishing, Halogen Free
Length	0.5 m
Material	PP
Slot Type	Flexible
Standards Met	UL 94 V-1
Trunking/Chain Type	Slotted Flexible Panel Trunking
Width	9 mm
Temperature Range	-20 to +70°C