

End clamp - E/MK 1 - 1421659

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



End clamp width: 6 mm, color: gray

Why buy this product

- Can be screwed onto NS 15 DIN rails
- Large-surface labeling
-



Key commercial data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 017918 021573
Weight per Piece (excluding packing)	2.6 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Dimensions

Height	18 mm
Length	21.2 mm
Width	6.1 mm

General

Material	PA
Coating	3.2 mm fixing hole
Color	gray
Tightening torque, min	0.4 Nm
Tightening torque max	0.5 Nm

End clamp - E/MK 1 - 1421659

Classifications

eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27141135
eCl@ss 5.1	27141145
eCl@ss 6.0	27141135
eCl@ss 7.0	27141135
eCl@ss 8.0	27141135

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC001041
ETIM 4.0	EC001041
ETIM 5.0	EC001041

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

Accessories

Accessories

Mounting rail

DIN rail, unperforated - NS 15 UNPERF 2000MM - 1401695



DIN rail, material: Steel, unperforated, height 5.5 mm, width 15 mm, length: 2 m

DIN rail perforated - NS 15 PERF 2000MM - 1401682



DIN rail, material: steel galvanized and passivated with a thick layer, perforated, height 5.5 mm, width 15 mm, length: 2000 mm

End clamp - E/MK 1 - 1421659

Accessories

DIN rail perforated - NS 15 AL PERF 2000MM - 1401763



DIN rail, material: Aluminum, perforated, height 5.5 mm, width 15 mm, length: 2 m

DIN rail perforated - NS 15 WH PERF 2000MM - 1204096



DIN rail, material: steel, perforated, height 5.5 mm, width 15 mm, length: 2 m

Drawings

End clamp - E/MK 1 - 1421659

Dimensional drawing

