



Sample photo

Order symbol: P 080806
Product nbr: 7094140
Description: Enclosure
Remarks: Polyester

EAN: 6418074004338
EI. number:
 Finland 3423655
 Denmark 8212005604
 Italy 7331010
 Sweden 2536205

Including: Base, cover with EPDM gasket and stainless steel cover screws.

Dimensions:		L	W	H	Rating:
mm:		75	80	55	Ingress Protection (EN 60529): IP 66/67
inch:		3	3.1	2.2	Impact Resistance (EN 50102): IK 08
Materials:					
Material:		GRP			
Base colour:		RAL 7001			
Cover colour:		RAL 7001			
Cover screws material:		Stainless steel			
Gasket material:		EPDM			
Temperatures:					
Short term:		-50 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-60 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
PM 0808		Mounting plate			
TRM 0808		DIN-15 Mounting rail			
MRS 28540		Wall fastening lug set			
Electrical insulation:		Totally insulated			
Halogen free (DIN/VDE 0472, Part 815):		Yes			
UV resistance:		UL 508			
Flammability Rating (UL 746 C 5):		UL 94 5V			
Glow Wire Test (IEC 695-2-1) °C:		960			
NEMA Class:		NEMA 1, 4, 4X, 12, 13			
Certificates:					

