


RSNA



	RSNA01RB	RSNA01NJ	RSNA02RB	RSNA250RB	RSNA580RB	RSNA505RB	SP1205SB
mm / M	50 x 100M	50 x 100M	50 x 100M	50 x 200M	80 x 500M	50 x 100M	Ø14 x 1200
Kgs	0.170	0.170		0.320	1.600	0.300	5.400



RSA



	RSA335RB	RSA335NJ
mm / M	50 x 33M	50 x 33M
Kgs	0.300	0.300



	RSA550KB	RSA550NJ
mm / M	50 x 5M	50 x 5M
Kgs	0.150	0.150