

TURCK

Level Sensors - Capacitive



Housing Style	Part Number	ID Number	Features	Embeddable Range (mm)	Nonembed. Range (mm)	Output
30 mm - Embeddable, Potted-In Cable 	BC10-M30K-VN4X	M2503024	Comp. Outputs	10	10	4-Wire DC NPN
	BC10-M30K-VP4X	M2503022	Comp. Outputs	10	10	4-Wire DC PNP
	BC10-M30K-AZ3X	M2503031		10	10	2-Wire AC N.O.
	BC10-M30K-RZ3X	M2503025		10	10	2-Wire AC N.C.

Level Sensors - Capacitive

Voltage	Switching Freq. (Hz)	Operating Current (mA)	Operating Temp. (°C)	Protection Class	Housing Material	Face Material	End Cap Material	Power LED	Output LED	Cable Length/Jacket	Wiring Diagram #	Wiring Diagrams
10-65 VDC	100	≤200	-25 to +70	IP67	CPB	PA 12-GF30	PA 66-GF25-V0	N/A	YE	2M/PVC	1	<p>Diagram 1</p> <p>Diagram 2</p>
10-65 VDC	100	≤200	-25 to +70	IP67	CPB	PA 12-GF30	PA 66-GF25-V0	N/A	YE	2M/PVC	2	<p>Diagram 3</p> <p>Diagram 4</p>
20-250 VAC	20	≤500	-25 to +70	IP67	CPB	PA 12-GF30	PA 66-GF25-V0	N/A	YE	2M/PVC	3	<p>Diagram 3</p> <p>Diagram 4</p>
20-250 VAC	20	≤500	-25 to +70	IP67	CPB	PA 12-GF30	PA 66-GF25-V0	N/A	YE	2M/PVC	4	<p>Diagram 3</p> <p>Diagram 4</p>

* Length in meters.