



Armstrong Black Oxidized C Hook Wrench with 1 1/4 → 3in Jaw Capacity

Features

- Incorporates One Adjustable Hook which is designed to Adjust Threaded Collars, Locknuts, Rings, Packing Nuts, in Industrial Applications.
- Manufactured From High Alloy Steel Using the Most Up-To-Date Manufacturing Process and Heat Treat for Greater Strength and Durability

Specification

Finish	Black Oxidized
Maximum Jaw Capacity	3in
Minimum Jaw Capacity	1 1/4in
Overall Length	8 1/8 in