

# Tamper-Resistant Construction Spec Grade Single Receptacles, Back & Side Wire, 15A, 125V, White

TR5251W



Tamper-Resistant Construction Spec Grade Single Receptacle Back & Side Wire  
15amp 125volt White



## features & benefits

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- .032 inch thick brass triple-wipe power contacts for lasting retention.
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive steel terminal screws. Side wire capability.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## specifications

### General Info

Color: white  
Type: Single, Receptacles  
Number Of Poles: 2  
Number Of Wires: 3  
Special Features: Tamper-Resistant,back,side wire

**Listing Agencies/Third Party Information**

CSA Listing Info: C22.2 No. 42  
CSA Standard: Yes  
Federal Spec: Yes  
Fed Spec Number: WC596  
UL Listing No: UL498  
UL Standard: Yes  
UN SPS C: 39121406  
UR: No

**Dimensions**

Depth U S: 1.19"  
Height U S: 3.28"  
Width U S: 1.296"

**Technical Information**

Amps: 15 Amp  
NEMA Configuration Number: 5-15R  
Volts: 125V  
Volts A C: 125  
Capacity: Single  
Grade Type: Construction

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant