



ENGLISH

Datasheet

RS Pro RS-1327K IR Thermometer

RS Stock No: 411-122



Product Details

RS Pro IR thermometer with socket for Type K thermocouple, features pocket sized pistol grip, built in laser sighting, backlit LCD display, auto HOLD, MAX / MIN reading, adjustable emissivity and high/low audible and visible alarm. It is supplied with PP3 battery, wrist strap, belt holster and instructions.

Features and Benefits

- Data memory (50 measurements) and read function from LCD display
- Selectable °C/°F display
- IR mode measuring range: -35 to 500°C
- Type K measuring range: -150 to 1350°C

**Specifications:**

Absolute Maximum Temperature Measurement	+1350°C
Best Accuracy	±2%
Data Storage	Yes
Dimensions	172 x 118 x 46 mm
Distance to Spot Ratio	12:1
Emissivity	0.17 to 1
Height	46 mm
Length	172 mm
Resolution	0.1°C
Temperature Scale	Centigrade, Fahrenheit
Weight	220 g
Width	118 mm
Standards Met	CE Certified