

Article Number:

21.15.0863-50



Description

Patch cable for networking connections between devices. Prepared double shielded Twisted Pair cable with screened RJ-45 connectors on both ends. Durable due to moulded kink protection. Flexible cable, suitable for narrow bending. High quality plugs with gold plated contacts. Contact settings 1:1, in accordance with the EIA/TIA 568 standard. Construction: 4-pair stranded copper wire. Complete braid shielding. Pairs shielded with aluminium clad polyester foil.

For a structured shielded Cat.6a cabling system we recommend to use the following components: ROLINE Cat.6a S/FTP Cable, Solid Wire, 300 m: 21.15.0881. ROLINE Flush Mount Wall Jack for Keystones: 25.16.8579; ROLINE Cat.6a Keystone, RJ-45, shielded: 21.11.0366; ROLINE Cat.6a 19" Keystone Patch Panel: 26.11.0368; ROLINE Cat.6a S/FTP Patch Cord, 5 m: 21.15.0865. Our in-house laboratory has tested these cable-plug combinations, in a Channel of 100 meters, in compliance with Class E specifications.

Technical Data - Overview

Product group	Twisted Pair Cable
Conveyance good	No
Shield type	SFTP
Transfer quality	Cat. 6a / Class EA
Quantity of wires	8
Conductor type	Wi re
Crossed	No
Colour (Cable)	grey
Colour (Spout)	grey
Halogen free cable	No
Connector Type RJ45	Standard

We reserve the right to amend any or all information without prior notice. Furthermore, all prices and offers are subject to change. We assume no responsibility for misprints or the accuracy of technical information. Product pictures and/or graphics are of an exemplary nature and can deviate from the original.