

S502UC-K15



Products Low Voltage Products and Systems Modular DIN Rail Products High Performance Circuit Breakers HPCBs

General Information

Extended Product Type:	S502UC-K15
Product ID:	2CCF009031R0001
EAN:	7612270302390
Catalog Description:	S502UC-K15 High Performance Circuit Breaker HPCB
Long Description:	The S500 high performance circuit breaker fulfills the requirement of larger short-circuit currents, thus in turn placing heavy demands on protective switchgear regarding safety, reliability and switching capacities. It is equipped with thermal and / or electromagnetic release to protect circuits, motors, switchgear and systems from the effect of overload and short circuit currents.

Ordering

EAN:	7612270302390
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85363020

Dimensions

Product Net Width:	50 mm
Product Net Depth:	92 mm
Product Net Height:	91 mm
Product Net Weight:	0.5 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	100 mm
Package Level 1 Length:	52 mm
Package Level 1 Height:	95 mm
Package Level 1 Gross Weight:	0.52 kg
Package Level 1 EAN:	7612270302390
Package Level 2 Units:	3

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

Technical

Standards:	IEC 60947-2, UL1077, CAN/CSA 22.0 No.35
Number of Poles:	2
Tripping Characteristic:	UC-K
Rated Current (I_n):	10 ... 15 A
Rated Operational Voltage:	500 V DC
Rated Short-Circuit Capacity (I_{cn}):	30 kA
Rated Ultimate Short-Circuit Breaking Capacity (I_{cu}):	30 kA

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CCC413003C0201
RoHS Information:	2CCC412001D0201

Classifications

ETIM 4.0:	EC000042 - Miniature circuit breaker (MCB)
ETIM 5.0:	EC000042 - Miniature circuit breaker (MCB)
Object Classification Code:	F

