

# Specifications for BMP71 Label Printer Labels

<b>Adhesive</b>	Permanent Acrylic
<b>Article No.</b>	115102
<b>Brady Material No.</b>	<a href="#">B-427</a>
<b>Material Type</b>	Self-laminating Vinyl
<b>Colour</b>	White/Transparent
<b>Finish</b>	Matt
<b>Order Reference</b>	M71-19-427
<b>Printable Area - Height (mm)</b>	9.53
<b>Printable Area - Width (mm)</b>	25.40
<b>Printer Compatibility</b>	BMP71
<b>Size - Height (mm)</b>	25.40
<b>Size - Width (mm)</b>	25.40
<b>Additional Information</b>	Self-Laminating;Self-Extinguishing;Excellent water & oil resistance;Excellent abrasion and smudge resistance
<b>Thickness (mm)</b>	0.102
<b>Total Qty per Pack</b>	250 Label(s) / Box
<b>Vertical Repeat (mm)</b>	28.58
<b>Wire Gauge</b>	12-10
<b>Approval/Compliance</b>	UL Recognised
<b>Ribbon Series</b>	M71-R4300
<b>Application</b>	Laboratory Identification; Voice & Data Communication; Wire & Cable Marking
<b>Environment</b>	Freezer; Liquid Nitrogen
<b>Industry</b>	Aerospace;Data/Telecommunications;Defence;Electrical;Healthcare;Laboratory;Mass Transit
<b>Laboratory Application</b>	Straws
<b>Description</b>	Labels for the BMP™71 Label Printer. Please Note: This material is UL Approved with its respective ribbon. See the Recommended Ribbon Series for the appropriate ribbon to

	use.
<b>Max. Characters per Line</b>	24
<b>Max. Lines of Text</b>	3
<b>Max. Service Temp. °C</b>	60
<b>Max. Wire/Cable Diameter (mm)</b>	5.10
<b>Min. Service Temp. °C</b>	-80
<b>Min. Wire/Cable Diameter (mm)</b>	2.70
<b>Shape</b>	Square
<b>Straw Size</b>	0.25 ml Straw
<b>Surface</b>	For smooth & textured/rough surfaces
<b>Voice/Data Application</b>	2 Pair Fibre