

R46_310, Film, Metallized Polypropylene, Safety, 10 uF, 10%, 310 VAC (X2), 630 VDC, 110°C, Lead Spacing = 37.5mm



Dimensions

L	41.5mm +0.3mm
H	45mm +0.1mm
T	30mm +0.3mm
S	37.5mm +/-0.4mm
LL	25mm +2/-1mm
F	1mm +/-0.05mm

Packaging Specifications

Packaging:	Tray
Packaging Quantity:	60

General Information

Supplier:	KEMET
Series:	R46_310
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	EMI Safety
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	ENEC, UL, cUL, CQC

Specifications

Capacitance:	10 uF
Capacitance Tolerance:	10%
Voltage AC:	310 VAC (X2)
Voltage DC:	630 VDC
Temperature Range:	-40/+110C
Rated Temperature:	110°C
Dissipation Factor:	0.10% 1kHz
Insulation Resistance:	3 GOhms
Max dV/dt:	100 V/us
Safety Class:	X2