



Price* : 28.21 GBP



Main

Range	TeSys
Device short name	GAC0
Product or component type	Auxiliary contact block
Product compatibility	TeSys GC TeSys GY
Mounting location	Right side
Pole contact composition	2 NO
[Ue] rated operational voltage	250 V
[Ith] conventional free air thermal current	5 A at ≤ 50 °C

Complementary

[Ui] rated insulation voltage	500 V - conforming to IEC 60947-5 500 V - conforming to VDE 0110
Mechanical durability	1 Mcycles
Connections - terminals	Screw clamp terminals cable 2.5 mm ² - cable stiffness: solid Screw clamp terminals cable 2.5 mm ² - cable stiffness: flexible
Tightening torque	0.8 N.m - on screw clamp terminals
Height	81 mm
Width	8.75 mm
Depth	60 mm
Product weight	0.016 kg

Environment

Standards	IEC 60947-5
Product certifications	CEBEC NF-USE OVE VDE

IP degree of protection	IP20 conforming to VDE 0106
Protective treatment	TC
Ambient air temperature for operation	-5...50 °C
Ambient air temperature for storage	-40...70 °C
Operating altitude	<= 3000 m without derating

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0607 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------