



421U BODY WITH HOSETAIL for metric tubing

		DN (mm)	Flow Rate (l/min)	ØD (mm)	E (mm)	F (mm)	ØG (mm)	L (mm)	 (kg)
9421U06 06		5,5	1250	6	26,0	17,0	31,5	88,5	0,070
9421U06 08		5,5	1250	8	26,0	17,0	31,5	88,5	0,070
9421U06 10		5,5	1250	10	26,0	17,0	31,5	88,5	0,070
9421U08 08		8,0	2250	8	26,0	22,0	36,5	95,0	0,100
9421U08 10		8,0	2250	10	26,0	22,0	36,5	95,0	0,124
9421U08 13		8,0	2250	13	30,0	22,0	36,5	99,0	0,125



421U BODY WITH HOSETAIL

maximum working pressure	bar 16	MPa 1,6	psi 232
working temperature	°C (Celsius) From -20 to 60	F (Fahrenheit) From -4 to 140	K (Kelvin) From 253 to 333
ball	stainless steel		
body	engineering grade polymer		
sub-base	nickel-plated brass		
'O'-rings	nitrile		
spring	stainless steel		