



## Enriched BRUTE® 167 L



- Built-in venting channels reduce force required to lift full liners by up to 50%.
- Liner cinches allow for one-step liner retention with no knot-tying.
- ProTouch™ Grips provide for comfortable lifting and dumping.
- Can be used with the full line of Brute® accessories.
- Weight limit : Up to 136.1 kg.
- CSFM approved when used with a 2647-88 dome top.

2645-60



2643-60

### PRODUCT INFORMATION

Ref	Designation	Material	Dimensions (cm)		Capacity	Colours	Pack
			External	Internal			
2643-60	Brute® Container	Polyethylene	Ø 61 x 80	Top : Ø 57 / Bottom : Ø 49 Height : 76	166.5 L		4
2645-60	Brute® Lid	Polyethylene	Ø 62.2 x 4	•	•		4

### SPARE PARTS

#### 2643-L1 Handle Cap for 2643-60 Brute

Acc./Comp. Code	Quantity	Description	Comments
60-2643-Y1 Red	1	Handle Cap with Screws	•

### SHIPMENT INFORMATION

	Country of Origin (CoO)	EAN Product Code	DUN Carton Code	Custom Code	Carton Dimensions	Weight (kg)	Vol. (M³)
2643-60 BLA	US	086876183566	10086876183563	3924909000	142.2 x 61 x 61	22.5	0.53
2643-60 BLU	US	086876183580	10086876183587	3924909000	142.2 x 61 x 61	22.5	0.53
2643-60 GRAY	US	086876183559	10086876183556	3924909000	142.2 x 61 x 61	22.5	0.53
2643-60 YEL	US	086876183573	10086876183570	3924909000	142.2 x 61 x 61	22.5	0.53
2645-60 BLA	US	086876183597	10086876183594	3924909000	62.86 x 62.86 x 26.67	4.7	0.11
2645-60 GRAY	US	086876187465	10086776187462	3924909000	62.86 x 62.86 x 26.67	4.7	0.11
2645-60 WHT	US	086876187496	10086876187493	3924909000	62.86 x 62.86 x 26.67	4.7	0.11