




LOC	DIST	REVISIONS					
AJ	16	P	LTR	DESCRIPTION	DATE	DWN	APVD
		B		REVISED PER ECO 08-027009	04NOV2008	DW	FB

- △ USE PRO-CRIMPER II: 354940-1
2. USE INSTRUCTION SHEET 408-9766
- △ SPECIAL PACKAGING: BULK PACKAGE 25 PIECES
- △ SPECIAL PACKAGING: BULK PACKAGE 100 PIECES




RECOMMENDED STRIP LENGTH
SCALE 4:1



RECOMMENDED STRIP LENGTH
SCALE 4:1
(FOR 5413589-5 ONLY)

4 3 2 1	RAYDEX/CDT RA7000	1.07	[.042]	5.41	[.213]	58425-1	-	-	8-221132-9	413657-2	9-413653-2	2-5413589-5
	3M TYPE 138	1.07	[.042]	4.52	[.178]	58425-2	227194-2	222001-4	9-413658-0	1-413657-5	9-413653-1	2-5413589-3
	CUSTOM CABLE: C/C=Ø.021, DIELECTRIC=Ø.122, JACKET=Ø.173	1.07	[.042]	5.41	[.213]	58425-1	-	-	9-221132-0	1-413657-0	9-413653-2	2-5413589-1
	BELDEN 8218 AND JIS 2.5C-2V	1.07	[.042]	4.52	[.178]	58425-2	-	-	9-221132-6	413657-4	9-413653-1	1-5413589-6
	JIS 3C-2V	1.07	[.042]	5.41	[.213]	58425-1	-	-	9-221132-4	1-413657-0	9-413653-2	1-5413589-1
	AT&T 735A C/C=Ø.016, DIELECTRIC=Ø.077, JACKET=Ø.130	1.07	[.042]	4.52	[.178]	58425-2	-	-	9-413658-2	413657-4	9-413653-1	1-5413589-0
	RG-59 TYPE WITH .031 DIA CENTER CONTACT, BELDEN 9266, 9240 & 9259	1.07	[.042]	6.47	[.255]	58425-1	-	-	9-221132-1	413657-8	9-413653-0	5413589-9
	RG-179/U, 179A/U, 179B/U, 187/U & 187A/U	1.07	[.042]	4.52	[.178]	58425-2	227194-2	222001-4	9-413658-0	413657-6	9-413653-1	5413589-8
	AT&T 734A	1.07	[.042]	6.47	[.255]	58425-1	-	-	9-221132-3	413657-8	9-413653-4	5413589-7
	TIMES RG-59/U, DOUBLE BRAID, .270 OD JACKET	1.07	[.042]	8.23	[.324]	58425-3	-	-	9-221132-2	413657-2	9-413653-0	5413589-6
	BELDEN 8281, 9231 & AT&T 728 AND JIS 5C-2V	1.07	[.042]	8.23	[.324]	58425-3	-	-	9-221132-2	413657-8	9-413653-3	5413589-5
	BELDEN 8218 AND JIS 2.5C-2V	1.07	[.042]	4.52	[.178]	58425-2	-	-	9-221132-6	413657-4	9-413653-1	5413589-3
	RG-59/U, 59A/U & 59B/U	1.07	[.042]	6.48	[.255]	58425-1	-	-	9-221132-1	413657-2	9-413653-0	5413589-2
	BELDEN 88241	1.07	[.042]	6.48	[.255]	58425-1	-	-	9-413658-3	413657-2	9-413653-0	5413589-1
FOR USE WITH CABLE		CONTACT CRIMP (SQUARE)	FERRULE CRIMP (HEX)	DIE SET 1	5 TUBING, PLASTIC QTY=1	4 TUBING QTY=1	3 FERRULE QTY=1	2 CONTACT QTY=1	1 PLUG ASSY QTY=1	PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DATE 22APR2005	BY VARELA - DOCKES		 Tyco Electronics Corporation Harrisburg, PA 17105-3608
		CHK 22APR2005	J. HAVENER		
DIMENSIONS: mm [INCHES]		APVD 22APR2005	NAME J. LIPPERT		PLUG, 75 OHM, HEX CRIMP, BNC
		PRODUCT SPEC			
		APPLICATION SPEC			
MATERIAL —		WEIGHT —	SIZE CAGE CODE DRAWING NO A1 00779 C5413589		RESTRICTED TO —
CUSTOMER DRAWING			SCALE 8:1 SHEET 1 OF 1 REV B		