

# TradeMaster Tamper- Resistant Combo Receptacle/USB Charger

TM8USBBKCC6



2 Standard type A USB's, 2.1 A or 2100mA, 10.5 watts. Combination with Decorator Tamper-Resistant 15 A AC Receptacle, Black.

## features & benefits

- Meets 2008 National Electrical Code Tamper-Resistant requirements.
- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- High-impact resistant thermoplastic construction.
- Extra-long strap.
- Quickloop wire looping aid.
- Long-term blade retention.
- Longer tri-drive screws for easier 12 AWG looping.
- Extra-large circuit break-off tabs.
- Side-access push wire release.
- Ultrasonic welding of face to back body.
- Side wire accepts #12 – #14 AWG solid wire.
- Push wire accepts #14 AWG solid only.
- Superior protection than traditional outlet caps or protection plates.
- Low profile face.
- Traditional contoured face (3232 models).
- Self-grounding models provide automatic ground clip.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## specifications

### General Info

Color: Black  
Type: Tamper-Resistant

**Listing Agencies/Third Party Information**

ETL Listing No: 4001804  
ETL Listed: Yes  
UL Listing No: In Process

**Dimensions**

Depth U S: 1.6"  
Height U S: 2.7"  
Width U S: 1.7"

**Technical Information**

Amps: 15 Amp

**Buy American Act Compliance**

Country of Origin: CHINA  
Buy American Act Status: No