



ENGLISH

Datasheet

Stock No: 389-870

RS Pro White Nylon Non-Releasable Cable Tie, 190mm x 4.8 mm



Product Details

Flame Retardant Cable Ties

Temperature rating -10 to +85°C

Nylon 6.6 cable ties with improved flame retardant properties. The ties are suitable for binding components or cable and have a non-release ratchet lock action.



ENGLISH

Specifications:

Length	190mm
Width	4.8 mm
Colour	White
Material	Nylon 66
Type	Non-Releasable
Quantity	100
Minimum Operating Temperature	-10°C
Maximum Operating Temperature	+85°C
Tensile Strength	215.6N
Maximum Bundle Diameter	49mm