

Datasheet

RS Pro 5A Radial Non-Resettable Wire Ended Fuse, 250 V

RS Stock No: **767-5165**



Product Details

RS Pro radial non-resettable fuse withstands currents up to 5 A and voltages up to 250 V. It has thermoplastic body for added durability. This slow blow fuse forms a convenient and reliable solution to a vast array of application requirements.

Features and Benefits

- Slow blow fuse
- Non-resettable
- Radial fuse
- Wire-ended

**Specifications:**

Body Diameter	8.35 mm
Body Height	7.7 mm
Body Material	Thermoplastic
Breaking Capacity (at Maximum Voltage Rating)	50 A at 250 V ac
Current Rating	5 A
Lead Orientation	Radial
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-55°C
Voltage Rating	250 V
Voltage Rating	250 V
Wire Diameter	0.62 mm
Wire Length	22 mm, 4.3 mm
Wire Pitch	5.08 mm
Fuse Type	Time Lag
Nominal Resistance	0.01 Ω
Standards Met	VDE, CSA, UL, CCC, KTL, PSE, RoHS