

HP Scanjet G2410 Flatbed Scanner



Scan photos, documents, drawings and more, with this affordable and easy-to-use scanner. Edit, organise and share your scans using HP Photosmart Essential software. Use one-touch buttons to scan and copy with 1200 dpi resolution, 48-bit colour.

The HP Scanjet G2410 Flatbed Scanner is designed for home and business users who want an affordable and easy way to convert documents, photos, drawings and other images into digital files for easy sharing, reprinting and storing.

Capture crisp, clear scans of photos and 3D objects, and turn documents into editable text.

Do even more than you imagined with this versatile and easy-to-use scanner. Get true-to-life results from your photos – ideal for reprints – with 1200 dpi resolution and 48-bit colour. Keep digital records of essential documents or convert documents and articles into text that can be edited using OCR technology. Scan 3D objects too – HP's dual-sensor CCD scanning technology gives you great results on open books and items such as framed pictures, jewellery and mementos.

Scan and copy at the touch of a button and connect easily via USB 2.0.

Enjoy the speed, ease-of-use and convenience of two intuitive one-touch buttons. Place photos or documents under the lid and press scan – it really is that simple. Get easy copying too – just press the copy button to send scans to your printer without needing to use your computer. Connect quickly and easily to your PC or Mac, and transfer scans at optimum speeds with USB 2.0 connectivity.

Edit, organise and share scans with easy-to-use HP Photosmart Essential software.

Make the very most of your photo scans – edit, print, organise and share them using the included HP Photosmart Essential software. Crop, fix and enhance your scans with a range of easy-to-use tools. Let friends and family view, save and order photos – without large attachments or slow downloads – at Snapfish¹, an on-line service of HP. Share full resolution files by attaching photos to emails.

¹ Snapfish availability varies by region.

Technical specifications

Scanner Type	Flatbed
Scan Technology	Charge Coupled Device (CCD)
Scan resolution	Optical: Up to 1200 dpi Hardware: Up to 1200 x 1200 dpi Enhanced: Unlimited
Bit depth	48-bit
Greyscale Levels	256
Scaling	10 to 2400% in 1% increments
Scan speed	10 x 15 cm colour photo to file: about 21 sec, OCR A4 text page to Microsoft® Word®: about 47 sec 10 x 15 cm colour photo to share/e-mail: about 34 sec, PDF to email about 76 sec
Preview Speed	<10 secs
ADF capacity	None
Document size	Maximum: 21.6 x 29.7 cm
Control panel	2 front-panel buttons (Scan, Copy)
Scan file format	Windows®: BMP, JPEG, GIF, TIFF, TIFF Compressed, PNG, PCX, FlashPix (FPX), PDF, PDF searchable, RTF, HTM, TXT; Macintosh: TIFF, PICT, JPEG, GIF, FlashPix, Plain Text, PDF, HTML, Rich Text
Photo enhancements	Red-Eye Removal, Adaptive Lighting, Software Dust and Scratch Removal, Faded Colour Restoration
Software included	HP Photosmart software for Microsoft® Windows® (Windows® 2000 support available as Web download) and Macintosh with integrated OCR (by I.R.I.S.)
Operating systems compatibility	Certified for Windows Vista™; Windows® XP Home, Windows® XP Professional, Windows® XP Professional x64, Windows® XP Media Center; Windows® 2000; Mac OS X, Mac OS X v10.3.9, 10.4 or higher
Minimum system requirements	Microsoft® Windows® XP, XP x64, 2000: 500 MHz processor, 256 MB RAM, 450 MB available hard disk space, USB port, CD-ROM drive, 800 x 600 SVGA monitor, 16-bit colour, Microsoft® Windows® Internet Explorer 6; Windows Vista™, Vista x64: 800 MHz processor, 512 MB RAM, 450 MB available hard disk space, CD-ROM drive, 800 x 600 SVGA monitor, DirectX 9 capable graphics, Microsoft® Internet Explorer 7 Mac OS X v10.3.9, 10.4; PowerPC G3, G4 and G5 processor, Intel® Core processor; 128 MB RAM (256 MB recommended and required for Mac OS X v10.4); 250 MB available hard disk space; built-in USB
Interface and connectivity	Standard: USB – compatible with USB 2.0 specifications
Dimensions (w x d x h)	458 x 275 x 615 mm
Weight	2.2 kg; packaged: 2.7 kg
Operating environment	Operating temperature: 10 to 35° C; storage temperature: -40 to 70° C Operating humidity: 15 to 85% RH; storage humidity: 0 to 90% RH
Power requirements	Universal AC adapter 100 to 240 VAC (50/60 Hz) input, 12 VDC, 1.25 amp output; consumption: 17 watts maximum
ENERGY STAR	Yes
Regulatory compliance information/safety	IEC 60950-1: 2001 and national derivatives, EN 60950-1: 2001, China (CCC), Russia (GOST), Taiwan (BSMI)
Electromagnetic compatibility	EU (CE certification of conformity), North America (FCC), Australia (SMA), New Zealand (SMA), Russia (GOST), Korea (MIC), Taiwan (BSMI)
Warranty	Standard one-year limited hardware warranty. Warranty and support options vary by product, country and local legal requirements.

Ordering information

L2694A	HP Scanjet G2410 Flatbed Scanner, USB 2.0 cable, power cord, power adaptor, printed setup and support guide, CDs with user instructions and software
---------------	--

Service & Support

UG080E	HP Care Pack, Next Business Day Exchange Service, 3 years
UG203E	HP Care Pack, Exchange Service (standard turn around time), 3 years
UG283E	HP Care Pack, Return to Depot Hardware Support Service, 3 years. (UG283E: Only Baltics, Greece, Poland, Turkey, EEM, Slovenia, Czech Republic, Slovakia, Hungary. UG080E/UG203E: Rest of Europe).

For a complete list of supplies and accessories, please refer to the HP website at <http://www.hp.com>

<http://www.hp.com>

