

Specifications for BMP41/BMP51/BMP53 Labelmaker Labels

Adhesive	Permanent Acrylic
Article No.	131587
Brady Material No.	B-427
Material Type	Self-laminating Vinyl
Colour	Black on White/Transparent
Finish	Matt
Order Reference	M-53-427
Printable Area - Height (mm)	25.40
Printable Area - Width (mm)	25.40
Printer Compatibility	BMP41; BMP51; BMP53
Size - Height (mm)	101.60
Size - Width (mm)	25.40
Additional Information	Self-laminating; Self-extinguishing; Excellent water & oil resistance; Excellent abrasion and smudge resistance
Thickness (mm)	0.102
Total Qty per Pack	70 Label(s) / Box
Vertical Repeat (mm)	104.78
Wire Gauge	3/0 to 400 kcmil
Approval/Compliance	UL Recognised
Adhesive (Y/N)	Yes
Application	Voice & Data Communication; Wire & Cable Marking
Max. Service Temp. °C	60
Max. Wire/Cable Diameter (mm)	24.30
Min. Service Temp. °C	-80
Min. Wire/Cable	10.80

Diameter (mm)	
Shape	Rectangle
Software	LabelMark
Surface	For smooth & textured/rough surfaces
Voice/Data Application	50 Pair Copper; 24 Pair Fibre; Backbone