






RECOMMENDED MOUNTING:


M4 FASTENER WITH 6.00 IN-LB [7.00 XGF-CM] OF TORQUE MAX.



CHARACTERISTICS

ELECTRICAL RATING	15A 250VAC UL APPROVED 15A 250VAC VDE APPROVED
TERMINAL	SCREW
OPER. FORCE MAX.	160 GMS
RELEASE FORCE MIN.	42 GMS
PRETRAVEL MAX.	.106 [2.7 mm]
OVERTRAVEL MIN.	.094 [2.4 mm]
MOVE. DIFF. MAX.	.019 [0.5 mm]
REST POSITION MAX.	1.280 [32.5 mm]
OPERATING POSITION	1.173 TO 1.205 [29.8 TO 30.6 mm]

DWN: J. DOLNIK
APVD: SB
DATE: 25-May-04



THE CONFIDENTIAL AND PROPRIETARY INFORMATION CONTAINED IN THIS DOCUMENT IS OWNED BY CHERRY ELECTRICAL PRODUCTS, A DIVISION OF THE CHERRY CORPORATION WHO MUST GIVE WRITTEN PERMISSION BEFORE THE DOCUMENT OR INFORMATION CAN BE COPIED, DISCLOSED OR USED IN ANY WAY.

TOLERANCE UNLESS SPECIFIED
X .XX ± .005 ± 5.0° ANGLES

CHERRY
ELECTRICAL PRODUCTS
11204 80TH AVENUE
PLEASANT PRAIRIE, WI 53158

SPEC DRAWING
C ITEM NO. GPTCRM01

C	13038	01-Jul-05	JED	SG
REV	PCN NO	DATE	PREP	APVD

PROJECT 715A

SCALE: 2:1 CH 1 OF 1

ORIGINAL ON PROVE